



Representative

**Catalog Number:** ST3/490-B  
**Product ID:** 7TAA087990R0470  
**UPC Number:** 70450840766  
**Status:** Active

PVC Coated Liquidtight Conduit Connector, 90 Degree, Pipe Size 3/4 Inch/21 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Steel Fitting, Light Blue

### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Ocal
Type	Liquidtight Conduit Fitting - 90 Degree
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure
Size	3/4 Inch/21mm
Connection	90 Degree
Material	Steel
Finish	PVC Coated
Color	Light Blue
Environmental Conditions	Hazardous Locations

### European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	21mm
Nominal size in inch	3/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Material housing	Steel
Surface protection	Other

### Packaging

Outer Quantity	50
Outer Dimensions (inches)	15.12x13.25x7
Weight Uom	0.41 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)