



Actual

Catalog Number: UB11/2-G
Product ID: 7TAA087590R0024
UPC Number: 70450841233
Status: Active

PVC Coated U-Bolt, Pipe Size 1-1/2 Inch/41 Metric, A Dimension 2.50 Inch/63.50 Millimeters, Gray

North American Specifications (UNSPSC)

UNSPSC	31161616 U bolts
IGCC	2803 U bolts
Brand Name	Ocal
Type	PVC Coated U-Bolt
Special Features	Nominal .040 Inch (40 mil) PVC Coating for Corrosion Protection
Application	Support and Attach Conduit Runs to Structural Beams
Material	Malleable Iron
Finish	PVC Coated Gray
Size	1-1/2 Inch/41mm
Diameter	2.5 in ; 63.5 mm
Number of Nuts	2
Nut Type	Square

European Specifications (ETIM)

ETIM	EC000464 Fixing clamp
Type of fastening	Screwing
Connection type construction part	Other
Tube/cable diameter	41-41mm
Hinging	N
Material	Other
Surface protection	Coated

Packaging

Outer Quantity	100
Outer Dimensions (inches)	16.5x14x7.25
Weight Uom	0.33 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com