



Actual

**Catalog Number:** NPL1/2X31/2-G  
**Product ID:** 7TAA087160R0049  
**UPC Number:** 70450839754  
**Status:** Active

PVC Coated Conduit Nipple, 1/2 Inch/16 Metric Pipe Size x 3-1/2 Inch/88.9 Millimeters Nipple Length, Nominal .002 Inch (2 mil) Blue Urethane on Interior, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Hot-Dip Galvanized Rigid Steel, Gray

- A nominal .002 (2 mil) blue urethane on the interior.
- Color coded thread protectors on each end.
- Blue urethane coating over threads.

### North American Specifications (UNSPSC)

UNSPSC	39131718 Electrical conduit nipple
IGCC	5753 Electrical conduit nipple
Brand Name	Ocal
Type	Conduit Fittings-PVC Coated
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings
Standard	cULus E46453, CSA, RoHS
Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized
Length	3-1/2 in ; 88.9 mm
Trade Size	1/2 Inch/16 Metric

### European Specifications (ETIM)

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	16
Material housing	Other
Surface protection	Hot dip galvanized
Model	Straight
Total length	88.9mm

### Packaging

Outer Quantity	100
Outer Dimensions (inches)	11.37x7.12x6.75
Weight Uom	25.63 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000549
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
 www.tnb.com

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email:techsupport@tnb.com