



Representative

Catalog Number: COND11/2SA-B
Product ID: 7TAA087000R0266
UPC Number: 70450802872
Status: Active

PVC Coated Conduit, Pipe Size 1-1/2 Inch/41 Metric, Outside Diameter with PVC 1.98 Inch/ 50.20 Millimeters, Nominal Wall Thickness with PVC .18 Inch/4.52 Millimeters, Length without Couplings 9 Feet 11 Inch/3.02 Meters, Aluminum, Light Blue

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Ocal
Type	Conduit-PVC Coated
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems
Standard	UL E221184
Trade Size	1-1/2 Inch
Outside Diameter	1.98 Inch/50.20mm
Inside Diameter	1.62 Inch/41.20mm
Length	9.91 ft ; 3.02 m
Material	Aluminum
Wall Thickness	0.18 Inch/4.52mm
Color	Light Blue

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal size in inch	1 1/2 inch
Outer diameter	50.20mm
Inner diameter	48.30mm
Material	Aluminium
Surface protection	Untreated
Sheathing material 2nd coating (exterior)	PVC
Colour	Blue
Bending strength	Rigid

Packaging

Outer Quantity	380
Outer Dimensions (inches)	120x20.5x8.5
Weight Uom	9.38 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000544
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com