



Actual

Catalog Number: NPL3/4X41/2-G
Product ID: 7TAA087160R0134
UPC Number: 70450839966
Status: Active

PVC Coated Conduit Nipple, 3/4 Inch/21 Metric Pipe Size x 4-1/2 Inch/114.3 Millimeters Nipple Length, Nominal .002 Inch (2 mil) Blue Urethane on Interior, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Hot-Dip Galvanized Rigid Steel, Gray

North American Specifications (UNSPSC)

UNSPSC	39131718 Electrical conduit nipple
IGCC	5753 Electrical conduit nipple
Brand Name	Ocal
Type	Conduit Fittings-PVC Coated
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings
Standard	cULus E46453, CSA, RoHS
Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized
Length	4-1/2 in ; 114.3 mm
Trade Size	3/4 Inch/21 Metric

European Specifications (ETIM)

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	21
Material housing	Other
Surface protection	Hot dip galvanized
Model	Straight
Total length	114.3mm

Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	44 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000549
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com