



Actual

Catalog Number: CB11/2-G
Product ID: 7TAA087620R0006
UPC Number: 70450835920
Status: Active

PVC Coated Clamp-Back Spacer, Pipe Size 1-1/2 Inch/41 Metric, Use with One-Hole Pipe Strap, Malleable Iron, Dark Gray

North American Specifications (UNSPSC)

UNSPSC	31161816 Spacers or standoffs
IGCC	2894 Spacers or standoffs
Brand Name	Ocal
Type	Clamp-Back Spacer
Special Features	PVC Coated for Corrosion Protection
Application	Provide Spacing for Airflow Between Conduit and Mounting Surface
Inside Diameter	1-1/2 Inch
Material	Iron

European Specifications (ETIM)

ETIM	EC001494 Spacer for cable protection tube
Suitable for pipe diameter	41-41mm

Packaging

Inner Dimensions (inches)	xx
Outer Quantity	25
Outer Dimensions (inches)	8.75x7.05x5.45
Weight Uom	0.23 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com