



Actual

**Catalog Number:** LRELL21/2X36SA-G  
**Product ID:** 7TAA087000R1035  
**UPC Number:** 70450801854  
**Status:** Active

Large Radius Elbow, 40 Mil PVC Coated, Pipe Size 2-1/2 Inch/63 Metric, Angle 90 Degrees, Radius 36 Inch/914.40 Millimeters, Offset 3 Feet 11 Inch/1,193.80 Millimeters, Straight End 11 Inch/279.40 Millimeters, Unbent Length 78 Inch/1,981.20 Millimeters, Rigid Aluminum, Gray

### North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5746 Electrical conduit elbow
Brand Name	Ocal
Type	Conduit Elbow - Large Radius
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting
Material	Aluminum
Color	Gray
Finish	PVC Coated
Length	78 in ; 1,981.2 mm
Trade Size	2-1/2 Inch/63mm
Connection	90 Degree Bend

### European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	63mm
Angle of bow	90°

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	1350 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000554
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)