



Representative

**Catalog Number:** COND11/2SA-R  
**Product ID:** 7TAA087000R0267  
**UPC Number:** 70450833105  
**Status:** Active

PVC Coated Conduit, Pipe Size 1-1/2 Inch/41 Metric, Outside Diameter with PVC 1.98 Inch/ 50.20 Millimeters, Nominal Wall Thickness with PVC .18 Inch/4.52 Millimeters, Length without Couplings 9 Feet 11 Inch/3.02 Meters, Aluminum, Red

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Ocal
Type	Conduit-PVC Coated
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems
Standard	UL E46453, CSA
Trade Size	1-1/2 Inch
Outside Diameter	1.98 Inch/50.20mm
Inside Diameter	1.62 Inch/41.20mm
Length	9.91 ft ; 3.02 m
Material	Aluminum
Wall Thickness	0.18 Inch/4.52mm
Color	Red

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal size in inch	1 1/2 inch
Outer diameter	50.20mm
Inner diameter	48.30mm
Material	Aluminium
Surface protection	Untreated
Sheathing material 2nd coating (exterior)	PVC
Colour	Other
Bending strength	Rigid

### Packaging

Inner Quantity	10
Outer Quantity	380
Outer Dimensions (inches)	120x20.5x8.5
Weight Uom	1.02 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000544
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)