



Representative

Catalog Number: ELL11/4SA-R
Product ID: 7TAA087000R0469
UPC Number: 70450837011
Status: Active

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 1-1/4 Inch/35 Metric, Angle 90 Degrees, Radius 7-1/4 Inch/184.15 Millimeters, Offset 9-1/2 Inch/241.30 Millimeters, Straight End 2-1/4 Inch/57.15 Millimeters, Unbent Length 15.89 Inch/403.56 Millimeters, Rigid Aluminum, Red

North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5746 Electrical conduit elbow
Brand Name	Ocal
Type	Conduit Elbow - Standard Radius
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting
Material	Aluminum
Color	Red
Finish	PVC Coated
Length	15.89 in ; 403.56 mm
Trade Size	1-1/4 Inch/35mm
Connection	90 Degree Bend

European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Colour	Red
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	35mm
Angle of bow	90°

Packaging

Inner Quantity	1
Outer Quantity	10
Outer Dimensions (inches)	15.875x14.625x8
Weight Uom	1.32 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000552
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com