



Representative

Catalog Number: CPL1/2-GST
Product ID: 7TAA087000R1648
UPC Number: 70450803457
Status: Active

PVC Coated Conduit Coupling, 1/2 Inch/16 Metric Coupling Size, 1.50 Inch/38.10 Millimeters Minimum Length of Metal, 3.75 Inch/95.25 Millimeters Total Minimum Length Including Sleeve, Straight Threads, Pressure Sealing Sleeves, Blue Urethane Coating on Interior and Threads, Galvanized Steel, Gray

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Brand Name	Ocal
Type	Conduit Coupling
Special Features	Pressure-Sealing Sleeves Protect Your Connection
Application	Corrosion-Protected Connections for Conduit Sections
Trade Size	1/2 Inch/16mm
Length	3.75 in ; 95.25 mm
Material	Steel
Color	Gray

European Specifications (ETIM)

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Steel
Surface protection	Continuously galvanized
Model	Thread
For nominal tube diameter	16mm
Two piece	N
With inspection opening and cover	N

Packaging

Outer Quantity	100
Outer Dimensions (inches)	14.87x13x6.75
Weight Uom	0.2 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000545
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com