



Actual

Catalog Number: ST11/2-LG
Product ID: 7TAA087990R0455
UPC Number: 70450801986
Status: Active

PVC Coated Liquidtight Conduit Connector, Straight, Pipe Size 1-1/2 Inch/41 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Steel Fitting, Light Gray

- A minimum of .040 inch (40 mil) PVC coating is bonded to the exterior.
- Double coated with a nominal .002 inch (2 mil) blue urethane on both the interior and exterior, before PVC coating is applied.
- Pressure-sealing sleeves are designed to protect the connection.
- PVC coated connectors are available in straight, 45 degree and 90 degree configurations
- Ocal uses T&B Industrial Liquidtight fittings to insure quality installations.

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Ocal
Type	Liquidtight Conduit Fitting - Straight
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure
Size	1-1/2 Inch/41mm
Connection	Straight
Material	Steel
Finish	PVC Coated
Color	Light Gray
Environmental Conditions	Hazardous Locations

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	41mm
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Steel
Surface protection	Other

Packaging

Outer Quantity	15
Outer Dimensions (inches)	13.5x7.5x7.62
Weight Uom	99 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com