



Actual

Catalog Number: NPL11/2X3SA-G
Product ID: 7TAA087000R1110
UPC Number: 70450839790
Status: Active

PVC Coated Conduit Nipple, 1-1/2 Inch/41 Metric Pipe Size x 3 Inch/76.2 Millimeters Nipple Length, Nominal .002 Inch (2 mil) Blue Urethane on Interior, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Blue Urethane Coating Over Threads, Rigid Aluminum, Gray

North American Specifications (UNSPSC)

UNSPSC	39131718 Electrical conduit nipple
IGCC	5753 Electrical conduit nipple
Brand Name	Ocal
Type	Conduit Fittings-PVC Coated
Special Features	A Minimum .040 Inch (40 Mil) PVC Coating on Exterior
Application	To Connect Two Fittings
Standard	UL E46453, CSA, RoHS
Material	Aluminum
Color	Gray
Finish	PVC Coated
Length	3 in ; 76.2 mm
Trade Size	1-1/2 Inch/41 Metric

European Specifications (ETIM)

ETIM	EC001469 Protective hose adapter
With outer thread	Y
Thread size outer thread metric	41
Material housing	Aluminium
Surface protection	Untreated
Model	Straight
Total length	76.2mm

Packaging

Outer Quantity	1
Outer Dimensions (inches)	1x1x1
Weight Uom	20 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000550
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
 www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com