



Representative

**Catalog Number:** SS11/2-W  
**Product ID:** 7TAA087000R1330  
**UPC Number:** 70450840488  
**Status:** Active

PVC Coated Strut Pipe Strap, Pipe Size 1-1/2 Inch/41 Metric, Use With Either 1-5/8 Inch or 1-1/2 Inch Strut, Steel, White

### North American Specifications (UNSPSC)

UNSPSC	31151901 Metal straps
IGCC	2727 Metal straps
Brand Name	Ocal
Type	Pipe Strap for Strut
Special Features	Combination Slot and Hex Head Bolt for Flexibility of Attachment
Application	Designed for Easy Attachment of Conduit to Strut
Standard	RoHS
Size	1-1/2 Inch/41 Metric
Material	Steel
Color	White

### European Specifications (ETIM)

ETIM	EC000464 Fixing clamp
Type of fastening	Clamping
Connection type construction part	Pipe/cable
Tube/cable diameter	41-41mm
Hinging	N
Material	Steel
Surface protection	Coated

### Packaging

Inner Dimensions (inches)	xx
Outer Quantity	25
Outer Dimensions (inches)	8.25x6.625x5.25
Weight Uom	30 lbs. per 100

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)