

Catalog Number: HUB11/2-GN
Product ID: 7TAA087990R0637
UPC Number: 70450803663
Status: Active

PVC Coated Zinc Hub Connector with Thermoplastic Insulated Throat, Pipe Size 1-1/2 Inch/41 Metric, Overall Diameter 2.75 Inch/69.85 Millimeters, Maximum Panel Thickness 0.25 Inch/6.35 Millimeters, Throat Diameter 1.53 Inch/38.86 Millimeters, Nitrile Rubber (Buna-N) Sealing Ring, Green

North American Specifications (UNSPSC)

| | |
|--------------------|---|
| UNSPSC | 39121311 Electrical fittings |
| IGCC | 4441 Electrical fittings |
| Brand Name | Ocal |
| Type | Hub Connector |
| Special Features | Hexagonal/Splined Body and Locknut Enables Fast and Easy Installation |
| Application | To Positively Bond Conduit to Box or Enclosure |
| Size | 1-1/2 Inch/41mm |
| Material | PVC Coated Zinc |
| Color | Green |
| Temperature Rating | 105 Degrees C |

European Specifications (ETIM)

| | |
|----------------------|--|
| ETIM | EC001180 Screw connection for protective metallic hose |
| Nominal diameter | 41mm |
| Nominal size in inch | 1 1/2 inch |
| Model | Straight |
| Revolving thread | N |
| Construction type | External thread |
| Material housing | Other |
| Surface protection | Other |

Packaging

| | |
|---------------------------|----------------|
| Outer Quantity | 25 |
| Outer Dimensions (inches) | 14.87x13x6.75 |
| Weight Uom | 0.88 lbs. Each |

Documents / Support Tools

| | |
|-----------------------------------|----------------------|
| Technical Drawing / Data Sheet US | Available on Website |
| Support/Tools | Available on Website |
| Catalog US | Available on Website |

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com