



Actual

Catalog Number: MINE21/2-G
Product ID: 7TAA087590R0011
UPC Number: 70450839692
Status: Active

PVC Coated Mini Conduit Hanger, Pipe Size 2-1/2 Inch/63 Metric, Rated for Loads up to 500 Pounds (226.80 Kilograms) with a Safety Factor of Three, Includes Stainless Steel Bolt and Nut, Dark Gray

North American Specifications (UNSPSC)

UNSPSC	39121701 Electrical hangers
IGCC	5026 Electrical hangers
Brand Name	Ocal
Type	Mini Conduit Hanger
Special Features	Includes Stainless Steel Bolt and Nut for Fast, Easy Installation
Application	Rated for Loads of Up to 500 Pounds/226.80kg with a Safety Factor of Three
Size	2-1/2 Inch/63mm
Material	Steel
Color	Dark Gray
Load	Up to 500 Pounds/226.80 Kilograms

European Specifications (ETIM)

ETIM	EC000464 Fixing clamp
Type of fastening	Clamping
Connection type construction part	Pipe/cable
Tube/cable diameter	63-63mm
Hinging	N
Material	Other
Surface protection	Coated

Packaging

Outer Quantity	25
Outer Dimensions (inches)	11.375x7.125x6.75
Weight Uom	40 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com