



Actual

Catalog Number: SS21/2-G
Product ID: 7TAA087620R0013
UPC Number: 70450840507
Status: Active

PVC Coated Strut Pipe Strap, Pipe Size 2-1/2 Inch/63 Metric, Use With Either 1-5/8 Inch or 1-1/2 Inch Strut, Steel, Gray

North American Specifications (UNSPSC)

UNSPSC	31151901 Metal straps
IGCC	2727 Metal straps
Brand Name	Ocal
Type	Pipe Strap for Strut
Special Features	Combination Slot and Hex Head Bolt for Flexibility of Attachment
Application	Designed for Easy Attachment of Conduit to Strut
Standard	RoHS
Size	2-1/2 Inch/63mm
Material	Steel
Color	Gray

European Specifications (ETIM)

ETIM	EC000464 Fixing clamp
Type of fastening	Clamping
Connection type construction part	Pipe/cable
Tube/cable diameter	63-63mm
Hinging	N
Material	Steel
Surface protection	Coated

Packaging

Outer Quantity	25
Outer Dimensions (inches)	11.6x7.5x8.35
Weight Uom	39 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com