



Representative

**Catalog Number:** CB11/2SA-G  
**Product ID:** 7TAA087750R0123  
**UPC Number:** 70450803325  
**Status:** Active

PVC Coated Clamp-Back Spacer, Pipe Size 1-1/2 Inch/41 Metric, Use with One-Hole Pipe Strap, Aluminum, Dark Gray

### North American Specifications (UNSPSC)

UNSPSC	31161816 Spacers or standoffs
IGCC	2894 Spacers or standoffs
Brand Name	Ocal
Type	Clamp-Back Spacer
Special Features	PVC Coated for Corrosion Protection
Application	Provide Spacing for Airflow Between Conduit and Mounting Surface
Inside Diameter	1-1/2 Inch
Material	Aluminum

### European Specifications (ETIM)

ETIM	EC001494 Spacer for cable protection tube
Suitable for pipe diameter	41-41mm

### Packaging

Outer Quantity	25
Outer Dimensions (inches)	8.25x6.62x5.25
Weight Uom	0.1 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)