



Representative

Catalog Number: CPL11/4SA-R
Product ID: 7TAA087000R0327
UPC Number: 70450836236
Status: Active

PVC Coated Conduit Coupling, 1-1/4 Inch/35 Metric Coupling Size, 1.91 Inch/48.41 Millimeters Minimum Length of Metal, 5.50 Inch/139.70 Millimeters Total Minimum Length Including Sleeve, Straight Threads, Pressure Sealing Sleeves, Blue Urethane Coating on Interior and Threads, Aluminum, Red

North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Brand Name	Ocal
Type	Conduit Coupling
Special Features	Pressure-Sealing Sleeves Protect Your Connection
Application	Corrosion-Protected Connections for Conduit Sections
Trade Size	1-1/4 Inch/35mm
Length	5.5 in ; 139.7 mm
Material	Aluminum
Color	Red

European Specifications (ETIM)

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Model	Thread
For nominal tube diameter	35mm
Two piece	N
With inspection opening and cover	N

Packaging

Inner Dimensions (inches)	xx
Outer Quantity	42
Outer Dimensions (inches)	16.5x13x7.5
Weight Uom	0.14 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000546
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com