



Representative

**Catalog Number:** COND3/4-W  
**Product ID:** 7TAA087940R0004  
**UPC Number:** 70450828102  
**Status:** Active

PVC Coated Conduit, Pipe Size 3/4 Inch/21 Metric, Outside Diameter with PVC 1.13 Inch/ 28.70 Millimeters, Nominal Wall Thickness with PVC .139 Inch/3.53 Millimeters, Length without Couplings 9 Feet 11-1/4 Inch /3.03 Meters, Hot-dip Galvanized Steel, White

- A minimum .040 inch (40 mil) PVC coating on the exterior.
- A nominal .002 inch (2 mil) blue urethane on the interior.
- Color coded thread protectors on each end.
- Blue urethane coating over Hot-Dip Galvanized threads.

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Ocal
Type	Conduit-PVC Coated
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems
Standard	cULus E46453, CSA
Trade Size	3/4 Inch
Outside Diameter	1.13 Inch/28.70mm
Inside Diameter	0.84 Inch/21.20mm
Length	9.94 ft ; 3.03 m
Material	Steel
Finish	Hot-Dip Galvanized
Wall Thickness	0.139 Inch/3.53mm
Color	White

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal size in inch	3/4 inch
Outer diameter	28.70mm
Inner diameter	26.70mm
Material	Steel
Surface protection	Other
Sheathing material 2nd coating (exterior)	PVC
Colour	White
Bending strength	Rigid

### Packaging

Inner Quantity	10
Outer Quantity	900
Outer Dimensions (inches)	120x18x7
Weight Uom	1.24 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000042
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)