



Representative

Catalog Number: HUB21/2-B
Product ID: 7TAA087000R0876
UPC Number: 70450838851
Status: Active

PVC Coated Zinc Hub Connector with Thermoplastic Insulated Throat, Pipe Size 2-1/2 Inch/ 63 Metric, Overall Diameter 3.75 Inch/95.25 Millimeters, Maximum Panel Thickness 0.25 Inch/6.35 Millimeters, Throat Diameter 2.41 Inch/61.21 Millimeters, Nitrile Rubber (Buna-N) Sealing Ring, Light Blue

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Ocal
Type	Hub Connector
Special Features	Hexagonal/Splined Body and Locknut Enables Fast and Easy Installation
Application	To Positively Bond Conduit to Box or Enclosure
Size	2-1/2 Inch/63mm
Material	PVC Coated Zinc
Color	Light Blue
Temperature Rating	105 Degrees C

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	63mm
Nominal size in inch	2 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Other
Surface protection	Other

Packaging

Inner Dimensions (inches)	xx
Outer Quantity	10
Outer Dimensions (inches)	14.875x13x6.75
Weight Uom	2.02 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com