

**Catalog Number:** HUB3/4-LG  
**Product ID:** 7TAA087990R0252  
**UPC Number:** 70450800568  
**Status:** Active

PVC Coated Zinc Hub Connector with Thermoplastic Insulated Throat, Pipe Size 3/4 Inch/21 Metric, Overall Diameter 1.44 Inch/36.58 Millimeters, Maximum Panel Thickness 0.19 Inch/ 4.83 Millimeters, Throat Diameter 0.78 Inch/19.81 Millimeters, Nitrile Rubber (Buna-N) Sealing Ring, Light Gray

**North American Specifications (UNSPSC)**

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Ocal
Type	Hub Connector
Special Features	Hexagonal/Splined Body and Locknut Enables Fast and Easy Installation
Application	To Positively Bond Conduit to Box or Enclosure
Size	3/4 Inch/21mm
Material	PVC Coated Zinc
Color	Light Gray
Temperature Rating	105 Degrees C

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	21mm
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Other
Surface protection	Other

**Packaging**

Outer Quantity	50
Outer Dimensions (inches)	13.5x7.5x7.62
Weight Uom	0.33 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
www.tnb.com

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com