



Actual

**Catalog Number:** COND11/4-G  
**Product ID:** 7TAA087010R0003  
**UPC Number:** 70450826104  
**EAN Number:** 05415022251180  
**Status:** Active

PVC Coated Conduit, Pipe Size 1-1/4 Inch/35 Metric, Outside Diameter with PVC 1.74 Inch/ 44.10 Millimeters, Nominal Wall Thickness with PVC .17 Inch/4.39 Millimeters, Length without Couplings 9 Feet 11 Inch/3.02 Meters, Hot-dip Galvanized Steel, Gray

- A minimum .040 inch (40 mil) PVC coating on the exterior.
- A nominal .002 inch (2 mil) blue urethane on the interior.
- Color coded thread protectors on each end.
- Blue urethane coating over Hot-Dip Galvanized threads.

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Ocal
Type	Conduit-PVC Coated
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems
Standard	cULus E46453, CSA
Trade Size	1-1/4 Inch
Outside Diameter	1.74 Inch/44.10mm
Inside Diameter	1.39 Inch/35.40mm
Length	9.91 ft ; 3.02 m
Material	Steel
Finish	Hot-Dip Galvanized
Wall Thickness	0.17 Inch/4.39mm
Color	Gray

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal size in inch	1 1/4 inch
Outer diameter	44.10mm
Inner diameter	42.20mm
Material	Steel
Surface protection	Other
Sheathing material 2nd coating (exterior)	PVC
Colour	Grey
Bending strength	Rigid

### Packaging

Inner Quantity	10
Outer Quantity	420
Outer Dimensions (inches)	120x19.5x7
Weight Uom	2.17 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000042
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)