



Actual

**Catalog Number:** ELL1/2-G  
**Product ID:** 7TAA087090R0000  
**UPC Number:** 70450836980  
**EAN Number:** 05415022251685  
**Status:** Active

Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 1/2 Inch/16 Metric, Angle 90 Degrees, Radius 4 Inch/101.60 Millimeters, Offset 6 Inch/152.40 Millimeters, Straight End 2 Inch/50.80 Millimeters, Unbent Length 10.28 Inch/261.19 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray

- A minimum .040 inch (40 mil) PVC coating on the exterior.
- A nominal .002 inch (2 mil) blue urethane on the interior.
- Ocal-Blue standard radius elbows are factory bent to reduce the time and wasted materials that can result from field bending.
- Color coded thread protectors on each end.

### North American Specifications (UNSPSC)

UNSPSC	39131717 Electrical conduit elbow
IGCC	5746 Electrical conduit elbow
Brand Name	Ocal
Type	Conduit Elbow - Standard Radius
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size
Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting
Standard	cULus E46453, CSA
Material	Steel
Color	Gray
Finish	Hot-Dipped Galvanized
Length	10.28 in ; 261.19 mm
Trade Size	1/2 Inch/16mm
Connection	90 Degree Bend

### European Specifications (ETIM)

ETIM	EC001493 Bend for cable protection tubes
Material	Metal
Material quality	Steel
Surface protection	Hot dip galvanized
Colour	Other
Model	Rigid
Shape	Outer - and inner side plain
Inner diameter	16mm
Angle of bow	90°

### Packaging

Inner Quantity	1
Outer Quantity	30
Outer Dimensions (inches)	14.5x8x8
Weight Uom	0.85 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000551
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)