

**Catalog Number:** ST3/490-LG  
**Product ID:** 7TAA087990R0471  
**UPC Number:** 70450800566  
**Status:** Active

PVC Coated Liquitight Conduit Connector, 90 Degree, Pipe Size 3/4 Inch/21 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Steel Fitting, Light Gray

**North American Specifications (UNSPSC)**

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Ocal
Type	Liquidtight Conduit Fitting - 90 Degree
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure
Size	3/4 Inch/21mm
Connection	90 Degree
Material	Steel
Finish	PVC Coated
Color	Light Gray
Environmental Conditions	Hazardous Locations

**European Specifications (ETIM)**

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	21mm
Nominal size in inch	3/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Material housing	Steel
Surface protection	Other

**Packaging**

Outer Quantity	50
Outer Dimensions (inches)	15.12x13.25x7
Weight Uom	0.41 lbs. Each

**Documents / Support Tools**

Technical Drawing / Data Sheet US	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
860 Ridge Lake Blvd.  
Memphis, TN 38120  
www.tnb.com

T&B Technical Support  
MS 3B-50  
860 Ridge Lake Blvd.  
Memphis, TN 38120

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com