



Representative

**Catalog Number:** CPL21/2SA-R  
**Product ID:** 7TAA087000R0336  
**UPC Number:** 70450836250  
**Status:** Active

PVC Coated Conduit Coupling, 2-1/2 Inch/63 Metric Coupling Size, 2.88 Inch/73.10 Millimeters Minimum Length of Metal, 6.88 Inch/174.70 Millimeters Total Minimum Length Including Sleeve, Straight Threads, Pressure Sealing Sleeves, Blue Urethane Coating on Interior and Threads, Aluminum, Red

### North American Specifications (UNSPSC)

UNSPSC	39131707 Electrical conduit coupling
IGCC	5548 Electrical conduit coupling
Brand Name	Ocal
Type	Conduit Coupling
Special Features	Pressure-Sealing Sleeves Protect Your Connection
Application	Corrosion-Protected Connections for Conduit Sections
Trade Size	2-1/2 Inch/63mm
Length	6.88 in ; 174.7 mm
Material	Aluminum
Color	Red

### European Specifications (ETIM)

ETIM	EC000939 Coupler for installation tubes
Material	Metal
Material quality	Aluminium
Surface protection	Untreated
Model	Thread
For nominal tube diameter	63mm
Two piece	N
With inspection opening and cover	N

### Packaging

Inner Dimensions (inches)	xx
Outer Quantity	17
Outer Dimensions (inches)	15.875x14.625x8
Weight Uom	0.96 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000546
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 860 Ridge Lake Blvd.  
 Memphis, TN 38120

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)