



Representative

**Catalog Number:** COND21/2-GN  
**Product ID:** 7TAA087950R0133  
**UPC Number:** 70450803766  
**Status:** Active

PVC Coated Conduit, Pipe Size 2-1/2 Inch/63 Metric, Outside Diameter with PVC 2.96 Inch/ 75.00 Millimeters, Nominal Wall Thickness with PVC .23 Inch/5.91 Millimeters, Length without Couplings 9 Feet 10-1/2 Inch/3.01 Meters, Hot-dip Galvanized Steel, Green

- A minimum .040 inch (40 mil) PVC coating on the exterior.
- A nominal .002 inch (2 mil) blue urethane on the interior.
- Color coded thread protectors on each end.
- Blue urethane coating over Hot-Dip Galvanized threads.

### North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Ocal
Type	Conduit-PVC Coated
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems
Standard	cULus E46453, CSA
Trade Size	2-1/2 Inches
Outside Diameter	2.96 Inch/75.00mm
Inside Diameter	2.49 Inch/63.20mm
Length	9.875 ft ; 3.01 m
Material	Steel
Finish	Hot-Dip Galvanized
Wall Thickness	0.23 Inch/5.91mm
Color	Green

### European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal size in inch	2 1/2 inch
Outer diameter	75.00mm
Inner diameter	73.00mm
Material	Steel
Surface protection	Other
Sheathing material 2nd coating (exterior)	PVC
Colour	Green
Bending strength	Rigid

### Packaging

Outer Quantity	170
Outer Dimensions (inches)	1x1x1
Weight Uom	5.88 lbs. Each

### Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000042
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

**For further technical assistance, please contact us...**

Memphis, TN 38120  
[www.tnb.com](http://www.tnb.com)

860 Ridge Lake Blvd.  
Memphis, TN 38120

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)