

Catalog Number: HUB11/2-LLG
Product ID: 7TAA087990R0665
UPC Number: 70450803747
Status: Active

PVC Coated Zinc Hub Connector with Thermoplastic Insulated Throat, Pipe Size 1-1/2 Inch/41 Metric, Overall Diameter 2.75 Inch/69.85 Millimeters, Maximum Panel Thickness 0.25 Inch/6.35 Millimeters, Throat Diameter 1.53 Inch/38.86 Millimeters, Nitrile Rubber (Buna-N) Sealing Ring, Light Gray (RAL7032)

North American Specifications (UNSPSC)

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Ocal
Type	Hub Connector
Special Features	Hexagonal/Splined Body and Locknut Enables Fast and Easy Installation
Application	To Positively Bond Conduit to Box or Enclosure
Size	1-1/2 Inch/41mm
Material	PVC Coated Zinc
Color	Light Gray (RAL 7032)
Temperature Rating	105 Degrees C

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	41mm
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Other
Surface protection	Other

Packaging

Outer Quantity	10
Outer Dimensions (inches)	14.87x13x6.75
Weight Uom	0.85 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

T&B Technical Support
MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com