



Actual

Catalog Number: ST11/2SA-G
Product ID: 7TAA087870R0005
UPC Number: 70450840651
Status: Active

PVC Coated Liquidtight Conduit Connector with Grounding Ring, Straight, Pipe Size 1-1/2 Inch/41 Metric, Minimum .040 Inch (40 mil) PVC Coating on Exterior, Aluminum Fitting, Dark Gray

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	Ocal
Type	Liquidtight Conduit Fitting - Straight
Special Features	Pressure-Sealing Sleeves Protect the Connection
Application	To Positively Bond Conduit to Box or Enclosure
Size	1-1/2 Inch/41mm
Connection	Straight
Material	Aluminum
Finish	PVC Coated
Color	Dark Gray
Environmental Conditions	Hazardous Locations

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal diameter	41mm
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Material housing	Other
Surface protection	Other

Packaging

Inner Dimensions (inches)	xx
Outer Quantity	15
Outer Dimensions (inches)	13.125x7.125x7.375
Weight Uom	0.56 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet Canada	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com