



Representative

Catalog Number: COND21/2SA-R
Product ID: 7TAA087000R0280
UPC Number: 70450833107
Status: Active

PVC Coated Conduit, Pipe Size 2-1/2 Inch/63 Metric, Outside Diameter with PVC 2.96 Inch/ 75.00 Millimeters, Nominal Wall Thickness with PVC .23 Inch/5.91 Millimeters, Length without Couplings 9 Feet 10-1/2 Inch/3.01 Meters, Aluminum, Red

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	Ocal
Type	Conduit-PVC Coated
Special Features	Color-Coded Thread Protectors
Application	Corrosion Protection for Electrical Systems
Standard	UL E221184
Trade Size	2-1/2 Inches
Outside Diameter	2.96 Inch/75.00mm
Inside Diameter	2.49 Inch/63.20mm
Length	9.875 ft ; 3.01 m
Material	Aluminum
Wall Thickness	0.23 Inch/5.91mm
Color	Red

European Specifications (ETIM)

ETIM	EC001179 Protective metallic hose
Nominal size in inch	2 1/2 inch
Outer diameter	75.00mm
Inner diameter	73.00mm
Material	Aluminium
Surface protection	Untreated
Sheathing material 2nd coating (exterior)	PVC
Colour	Other
Bending strength	Rigid

Packaging

Inner Quantity	10
Outer Quantity	170
Outer Dimensions (inches)	120x18.5x9
Weight Uom	2.06 lbs. Each

Documents / Support Tools

Technical Drawing / Data Sheet	WSD-000544
Technical Drawing / Data Sheet Canada	Available on Website
Support/Tools	Available on Website
Catalog US	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com