



⌘ HOOK-UP WIRE

STYLE 1015/1230 600 VOLTS (1032 1000 VOLTS 90c)

Ⓢ CSA STYLE TEW AWM MTW VW-1

DESCRIPTION:

Stranded tinned copper, color coded
PVC insulation.

CHARACTERISTICS:

Temperature Rating — 40°C to +105°C

Resistant to acids, alkalis, oil, flame,
moisture and fungus

* 1028

† UL1283

†† UL1284

OLYMPIC NO.	CONDUCTOR SIZE	STRAND	NOM. WALL THICKNESS	NOM. O.D.
360	24	7/32	.031"	.088"
361	22	7/30	.031"	.095"
362	20	10/30	.031"	.102"
363	18	16/30	.031"	.112"
364	16	26/30	.031"	.125"
365	14	41/30	.031"	.142"
366	12	65/30	.031"	.158"
367	10	105/30	.031"	.183"
* 368	8	133/29	.045"	.250"
† 368/6	6	133/27	.062"	.335"
† 368/4	4	133/25	.062"	.395"
†† 368/2	2	133/23	.060"	.440"
†† 368/1	1	259/25	.080"	.525"
†† 368/10	1/0	1045/30	.080"	.574"
†† 368/20	2/0	1330/30	.080"	.620"
†† 368/30	3/0	1672/30	.080"	.670"
†† 368/40	4/0	2109/30	.080"	.730"

STYLE 1061 - SEMI-RIGID PVC 300 VOLTS 80°C

Ⓢ STYLE SR-PVC & MIL-W-16878 "B"

DESCRIPTION:

Stranded tinned copper, color coded,
semi-rigid PVC insulation

CHARACTERISTICS:

Temperature Rating — -10°C to +80°C, 300 volts
in business machine or electronic computers only.

APPLICATIONS:

Internal wiring of computers, electric book-keeping,
accounting machines, and other office and
control equipment.

OLYMPIC NO.	CONDUCTOR SIZE	STRAND	NOM. WALL THICKNESS	NOM. O.D.
359	28	7/36	.009"	.035"
373	26	7/34	.009"	.039"
370	24	7/32	.009"	.044"
372	22	7/30	.009"	.050"
374	20	7/28	.009"	.057"
375	18	19/30	.009"	.066"
376	16	19/29	.009"	.078"
371	24	Solid	.009"	.043"
369	26	Solid	.009"	.038"