




RETRACTILE CORDS

TPR JACKET POWER CORDS – Retracted Lengths 1, 2 & 4 Feet – Extended Lengths 5, 10 & 20 Feet

UNSHIELDED



DESCRIPTION:

Long-lasting service is assured with this quality multiconductor power cord. Each conductor is stranded copper, with TPR insulation, and a rugged weather and oil resistant TPR jacket overall.

APPLICATION:

Used on electric tools, portable drills, soldering irons, electrical appliances, household appliances, etc., to eliminate loose hanging wires and to prevent wires from tangling and twisting.

CHARACTERISTICS:

Suggested operating temperature: -20°C to +105°C

OLYMPIC NO.			NO. OF COND.	CONDUCTOR SIZE STRAND		UL/CSA TYPE	AMP RATING	VOLT RATING	NOM. COIL O.D.	NOM. O.D. CORD
1 FT. LENGTHS	2 FT. LENGTHS	4 FT. LENGTHS								
6310E			2	18	41/34	SVEO/SVTO	7	300	7/8"	.25"
6311E			3	18	41/34	SJEOW/SJTO	7	300	1-3/8"	.330"
6312E			3	16	65/34	SJEOW/SJTO	10	300	1-3/8"	.345"
6313E	6314E		2	18	41/34	SVEO/SVTO	7	300	7/8"	.250"
6315E	6316E		3	18	41/34	SVEO/SVTO	7	300	1"	.270"
6350E	6351E		2	18	41/34	SJEOW/SJTO	7	300	1"	.300"
6317E	6318E		3	18	41/34	SJEOW/SJTO	7	300	1-3/8"	.330"
6319E	6320E		4*	18	41/34	SJEOW/SJTO	5.6	300	1-3/8"	.355"
6352E	6353E		2	16	65/34	SJEOW/SJTO	10	300	1-1/8"	.315"
6321E	6322E		3	16	65/34	SJEOW/SJTO	10	300	1-3/8"	.345"
6354E	6355E		4*	16	65/34	SJEOW/SJTO	8	300	1-3/8"	.410"
6356E	6357E		3	16	65/34	SEOW/STOW	10	600	1-1/2"	.400"
6358E	6359E		4*	16	65/34	SEOW/STOW	8	600	1-1/2"	.420"
6360E	6361E		3	14	41/30	SEOW/STOW	15	600	2-1/8"	.540"
6362E	6363E		4*	14	41/30	SEOW/STOW	12	600	2"	.570"

*If all four conductors normally carry current, amp rating is as shown. If one lead is used as a ground, amp rating is the same as 2 and 3 conductor cords.

A 12" retracted length with a 12" straight lead on each end for easy stripping and termination. Cord extends to approximately 6 feet.

COLOR CODE:

- 1 - Black
- 2 - White
- 3 - Green
- 4 - Red