




RETRACTILE CORDS

UNSHIELDED PLASTIC JACKETED MINIATURE CORDS UL LISTED



Stranded tinned copper,
polypropylene insulated,
black PVC jacketed.
-20°C +80°C

COLOR CODES: Black,
White, Red, Green, Orange,
Blue, Yellow, Brown, Grey,
Pink, Violet, Tan

OLYMPIC NO.	AVAIL. LENGTHS (RETRACTED) (INCHES)	NO. OF COND.	AWG NO.	MAX WORKING VOLTAGE	STRAND NO./AWG	COND. AMP RATING	CABLE O.D. (INCHES)	COIL O.D. (INCHES)
6516P	48,36,24,12	2	28	300	7/36	1/2	.140	1/2
6517P	48,36,24,12	3	28	300	7/36	1/2	.150	1/2
6518P	48,36,24,12	4	28	300	7/36	1/2	.155	1/2
6519P	48,36,24,12	5	28	300	7/36	1/2	.165	9/16
6520P	48,36,24,12	6	28	300	7/36	1/2	.180	5/8
6521P	48,36,24,12	7	28	300	7/36	1/2	.180	5/8
6522P	48,36,24,12	8	28	300	7/36	1/2	.195	5/8
RETRACTED - EXTENDED RATIO (1 TO 5)								
48" - 20'	36" - 15'	24" - 10'		12" - 5'				
STRAIGHT LEAD LENGTHS								
6"	6"	6"		12"				

UNSHIELDED PLASTIC or TPE JACKETED COMMUNICATIONS & ELECTRONIC CONTROL CORDS



UL LISTED
Stranded tinned copper,
polypropylene insulated,
PVC: -20°C + 80°C
or TPE jacketed: -20°C + 105°C

COLOR CODES: Black,
White, Red, Green, Orange,
Blue, Yellow, Brown, Grey,
Pink, Violet, Tan, White/Black,
Red/Black, Green/Black

*Black PVC jacket
**Black TPE jacket, Oil Resistant

OLYMPIC NO.	AVAIL. LENGTHS (RETRACTED) (INCHES)	NO. OF COND.	AWG NO.	MAX WORKING VOLTAGE	NOM. AREA (mm)	STRAND NO./AWG	COND. AMP RATING	CABLE O.D. (INCHES)	COIL O.D. (INCHES)
* 6370P ** 6382P	48,36,24,12	2	23	300	.259	21/36	1	.180	5/8
* 6371P ** 6383P	48,36,24,12	3	23	300	.259	21/36	1	.190	11/16
* 6372P ** 6384P	48,36,24,12	4	23	300	.259	21/36	1	.200	11/16
* 6373P ** 6385P	48,36,24,12	5	23	300	.259	21/36	1	.215	3/4
* 6374P ** 6386P	48,36,24,12	6	23	300	.259	21/36	1	.230	7/8
* 6375P ** 6387P	48,36,24,12	7	23	300	.259	21/36	1	.230	7/8
* 6376P ** 6388P	48,36,24,12	8	23	300	.259	21/36	1	.245	7/8
* 6377P ** 6389P	48,36,24,12	10	23	300	.259	21/36	1	.280	15/16
* 6378P ** 6390P	48,36,24,12	12	23	300	.259	21/36	1	.285	1
* 6379P ** 6391P	48,36,24,12	15	23	300	.259	21/36	1	.310	11/16