

Non-metallic nylon conduit system

Nylon fittings for XESX conduit

Type NENV Straight male fitting

Material: Anti-Static Nylon 12 with nickel plated brass thread

Part no.	Metric Thread Size (mm)	Fits to Conduit Size (mm)		Thread Length (mm)	Overall Length (mm)
		NW	Metric		
NENV0202	M12x1.5	10	12	10.0	40.0
NENV0203	M16x1.5	10	12	10.0	40.0
NENV0303	M16x1.5	12	16	10.0	43.0
NENV0304	M20x1.5	12	16	10.0	43.0
NENV0404	M20x1.5	17	20	10.0	51.0
NENV0405	M25x1.5	17	20	11.0	51.0
NENV0505	M25x1.5	23	25	11.0	52.0
NENV0506	M32x1.5	23	25	13.0	54.0
NENV0606	M32x1.5	29	32	13.0	56.0
NENV0607	M40x1.5	29	32	13.0	57.3
NENV0707	M40x1.5	36	40	13.0	71.4
NENV0708	M50x1.5	36	40	14.0	72.4
NENV0808	M50x1.5	48	50	14.0	72.4
NENV0809	M63x1.5	48	50	14.0	72.4



Type NEIR Straight female fitting

Material: Anti-Static Nylon 12 with nickel plated brass thread

Part no.	Metric Thread Size (mm)	Fits to Conduit Size (mm)		Thread Length (mm)	Overall Length (mm)
		NW	Metric		
NEIR0303	M16x1.5	12	16	9.0	41.0
NEIR0404	M20x1.5	17	20	10.0	50.0
NEIR0505	M25x1.5	23	25	10.0	56.0
NEIR0606	M32x1.5	29	32	11.0	55.5
NEIR0707	M40x1.5	36	40	13.0	71.0
NEIR0808	M50x1.5	48	50	15.0	73.0

