


Connectors NPT, metal thread

Type VNV

Type VNV - Connector straight, metric metal thread

| | Order no. IP68, black ⁴ | Thread NPT | Fits to conduit size | | Thread length (mm) | Overall length (mm) |
|---|---------------------------------------|---------------|----------------------|--------|--------------------------|---------------------------|
| | | | NW | Metric | | |
|  | NVNV-N022 | ½" | 12 | 16 | 15.4 | 48.1 |
| | NVNV-N027 | ½" | 17 | 20 | 15.4 | 56.4 |
| | NVNV-N043 | ¾" | 23 | 25 | 15.7 | 58.7 |
| | NVNV-N069 | 1" | 29 | 32 | 19.6 | 63.9 |
| | NVNV-N076 | 1¼" | 36 | 40 | 20.2 | 78.6 |
| | NVNV-N088 | 1½" | 48 | 50 | 20.6 | 79.0 |
| | NVNV-N098 | 2" | 48 | 50 | 21.4 | 79.8 |

Approvals



For applications in railway vehicles and heavy machine construction
High thread and system connection strength

⁴ IP68GT available. Please add
"GT" prior to the thread length
(for example NVNV-N022GT)