


Connectors GAS, polyamide thread


Type VN & VA

Type VN - Connector straight, GAS thread

	Order no. IP66 ①	Order no. IP68 ① ②	Thread GAS	Fits to conduit size		Thread length (mm)	Overall length (mm)
				NW	Metric		
	BVND-G00MGT	BVNV-G00M	¼"	07	10	11.0	34.5
	BVND-G000GT	BVNV-G000	¼"	10	12	11.0	36.5
	BVND-G010GT	BVNV-G010	⅜"	10	12	11.0	36.5
	BVND-G012GT	BVNV-G012	⅜"	12	16	11.0	39.0
	BVND-G022GT	BVNV-G022	½"	12	16	13.0	41.0
	BVND-G027GT	BVNV-G027	½"	17	20	13.0	49.5
	BVND-G043GT	BVNV-G043	¾"	23	25	14.0	54.0
	BVND-G069GT	BVNV-G069	1"	29	32	15.0	56.0
	BVND-G076GT	BVNV-G076	1¼"	36	40	18.0	71.0
	BVND-G088GT	BVNV-G088	1½"	48	50	18.0	71.5
	BVND-G098GT	BVNV-G098	2"	48	50	18.0	71.5

For cable protection systems in a wide range of applications

Type VA - Connector 45° elbow, GAS thread

	Order no. IP66 ①	Order no. IP68 ① ②	Thread GAS	Fits to conduit size		Thread length (mm)	Overall length (mm)
				NW	Metric		
	BVAD-G000GT	BVAV-G000	¼"	10	12	11.0	43.5 x 37.0
	BVAD-G012GT	BVAV-G012	⅜"	12	16	11.0	48.0 x 40.0
	BVAD-G027GT	BVAV-G027	½"	17	20	13.0	57.5 x 51.5
	BVAD-G043GT	BVAV-G043	¾"	23	25	14.0	67.0 x 60.0
	BVAD-G069GT	BVAV-G069	1"	29	32	15.0	73.5 x 67.0
	BVAD-G076GT	BVAV-G076	1¼"	36	40	18.0	91.5 x 85.5
	BVAD-G088GT	-	1½"	48	50	18.0	99.0 x 96.0
	BVAD-G098GT	BVAV-G098	2"	48	50	18.0	99.0 x 101.0

For cable protection systems in a wide range of applications

① Please replace "B" for black with "S" for grey in front of the order no.

② IP68GT available. Please add "GT" after the order no.