



PRODUCT-DETAILS

BVNZ-M406S

FTNG STR W/SR PA6 NW36 M40 IP68 bl



General Information

Extended Product Type:	BVNZ-M406S
Product ID:	7TAA292150R0321
EAN:	7630030230783
Catalog Description:	FTNG STR W/SR PA6 NW36 M40 IP68 bl
Long Description:	Fitting PMAFIX, Straight with Strain Relief, Polyamide 6, Metric Thread M40x1.5 , for Corrugated Conduits Size NW36, Clamping Range 22.0-32.0 mm, IP68, Color Black, Packaging Unit 20 pcs
Display Name:	BVNZ-M406S

Additional Information

Product Main Type:	PMA Flexible Cable Protection
Application:	For Use In Machine and Plant Construction
Product Type:	Connectors-Strain Relief

Ordering

EAN:	7630030230783
UPC:	786209952776

Technical

Color:	Black
Material:	Polyamide 6
Size:	NW36 , M40 Thread

Environmental

WEEE Category:	Product Not in WEEE Scope
RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units:	20 EA
Package Level 1 EAN:	7630030230783
Package Level 1 Height:	0 mm 0 in
Package Level 1 Depth / Length:	0 mm 0 in
Package Level 1 Width:	0 mm 0 in

Certificates and Declarations

Data Sheet, Technical Information:	BVNZ-M406S
Instructions and Manuals:	BVNZ-M406S
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC001176 - Screw connection for corrugated plastic hose
ETIM 9:	EC001176 - Screw connection for corrugated plastic hose
UNSPSC:	39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems > PMA Flexible Cable Protection

