

# JENQ-M207-10



PMAOXC Fitting,V2A/V4A,M20,NW17



## General Information

Extended Product Type	JENQ-M207-10
Product ID	7TCA292000R0464
EAN	7630031218230
Catalog Description	PMAOXC Fitting,V2A/V4A,M20,NW17
Long Description	Hygienic Conduit Fitting for Overextruded Conduit, Straight with External Male Thread, Conduit Size NW17, M20x1.5 Thread, Thread Length 10 Millimeters, IP68, IP69 Rating, Outer Layer 316 Stainless Steel, Inner Layer 303 Stainless Steel, Seal Elastomer, Metallic with Blue Seal

## Ordering

EAN	7630031218230
Minimum Order Quantity	1 piece
Customs Tariff Number	7307290090

## Dimensions

Product Net Weight	122.471 g
--------------------	-----------

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	25.4 mm
Package Level 1 Height	25.4 mm
Package Level 1 Depth / Length	25.4 mm
Package Level 2 Units	50 piece
Package Level 2 Width	508 mm
Package Level 2 Height	558.8 mm
Package Level 2 Depth / Length	762 mm

## Additional Information

Brand / Label	PMA
Color	Metallic
Function	For Food Zone, Non Contact Application Areas
Insulation Class	IP68, IP69
Material	Stainless Steel

Product Main Type	PMA FLEXIBLE CABLE PROTECTION
Product Name	SS FITTING FOR CONDUIT
Product Type	Straight Fitting
Standards	FDA 21 CFR / EU 10/2011 compliant sealing materials; ECOLAB certificate
UPC	786210180427

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	JENQ-M207-10
Instructions and Manuals	JENQ-M207-10

---

### Classifications

ETIM 6	EC001176 - Screw connection for corrugated plastic hose
ETIM 7	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

---

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

