

NENV0203



EX STR MALE FTNG NC12,M16 BLK



Product image
not available

General Information

Extended Product Type	NENV0203
Product ID	7TCA297120R0337
EAN	5011949239838
Catalog Description	EX STR MALE FTNG NC12,M16 BLK
Long Description	Conduit Fitting, Straight with External Male Thread, Conduit Size 12mm, M16 Thread, Minimum Bore 10mm, Suitable for Unbraided Nylon Conduit, Approved for Zone 1 and 2, Zone 21 and 22, IP68 Rating, Modified Nylon 12 with Nickel Plated Threads, Black

Ordering

EAN	5011949239838
Minimum Order Quantity	10 piece
Customs Tariff Number	3917400090

Dimensions

Product Net Weight	45.36 g
--------------------	---------

Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	302.26 mm
Package Level 1 Height	200.66 mm
Package Level 1 Depth / Length	210.82 mm
Package Level 2 Units	400 piece
Package Level 2 Width	401.32 mm
Package Level 2 Height	302.26 mm
Package Level 2 Depth / Length	210.82 mm

Additional Information

Brand / Label	Kopex
Color	Black
Function	For Indoor and Outdoor Applications
Insulation Class	IP68
Material	Modified Nylon 12 with Nickel Plated Threads

Product Main Type	PMA FLEXIBLE CABLE PROTECTION
Product Name	NYLON EX FITTING
Product Type	Straight Conduit Fitting with Male Thread
Special Functions	Nickel Plated Threads for Extra Stength
Standards	ATEX:SEV15ATATEX0121, IECEX:IECEX SEV15.0009, Ex eb IIC, Ex tb IIIC

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	NENV0203
Instructions and Manuals	NENV0203

Classifications

ETIM 6	EC001176 - Screw connection for corrugated plastic hose
ETIM 7	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image
not available