

XCYLG-36BB.30



CONDUIT CRSE PA6/PO NW36 30M BLK/BL

General Information

Extended Product Type	XCYLG-36BB.30
Product ID	7TAA292240R0278
EAN	7630030282690
Catalog Description	CONDUIT CRSE PA6/PO NW36 30M BLK/BL
Long Description	Coarse Profile Three Layer Corrugated Medium-Wall Very Flexible Conduit, (XCYL) Material - Outer Layer - Polyamide 6, Intermediate Layer - Bonding Compound, Inner Layer - Polyethylene Color - Outer Layer - Black, Inner Layer - Blue, Conduit Size NW - 36

Ordering

EAN	7630030282690
Minimum Order Quantity	36 piece
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	49.896 g
--------------------	----------

Container Information

Package Level 1 Units	1 piece
Package Level 2 Units	6 piece
Package Level 2 Width	799.998 mm
Package Level 2 Height	780.009 mm
Package Level 2 Depth / Length	1199.998 mm

Additional Information

Brand / Label	PMA
Color	Black
Function	Machine
Material	Outer Layer Polyamide 6, Inner Layer Polyethylene
Product Main Type	PMA FLEXIBLE CABLE PROTECTION
Product Name	PA FLEX TUBING
Product Type	Medium Wall Conduit
UPC	786209977649

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	XCYLG-36BB.30
Instructions and Manuals	XCYLG-36BB.30

Classifications

ETIM 6	EC001175 - Corrugated plastic hose
ETIM 7	EC001175 - Corrugated plastic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

