



NEW!
Pre-set units
for Belden
179DT mini-
75 ohm

Memory Cassette

- Screws adjust cutting depth of the blades
- Once set, mark for specific cable & store for next use
- Maintain separate memory cassettes for each cable type to quickly change applications without first fine adjusting




Y-block –
inserts into tool
to tighten up
rollers for smaller
cable sizes

CST Strippers

Our CST series coaxial strippers are designed for the professional and they are the standard for the broadcast industry. The CST is a fixed-blade system that accommodates 0.1"-0.315" (2.5-8.0 mm) cable diameters including RG58/59/62AU, RG6 and RG6 Quad, RG174, Belden 1505A, 1855A and 8281*.

- Cam adjustment ensures precise hold on cable
- Memory blocks reduce set-up time and are easy to interchange and mark for various applications
- Blades are two-sided for longer use
- No cable jacket distortion during stripping process
- Blade cassettes easy to change
- Lifetime warranty on frame; one-year warranty on cassettes



Technical	Weight	Length
CST strippers	2.4 oz. (65 g)	4" (100 mm)
CST replacement cassettes	1 oz. (2.8 g)	1.34" (34 mm)

Ordering	Tool w/blade	Blade cassette only	Common Uses
CST green 3 level (A=.279, B=.201)	1240	2240	Common 2- & 3-piece
CST blue 2 level (A=.256)	1241	2241	CATV "F" connectors
CST yellow 2 level (A=.472)	1242	2242	
CST brown 3 level (A=.295, B=.137)	1243	2243	
CST red 2 level (A=.236)	1244	2244	
CST gray 2 level (A=.153)	1246	2246	
CST orange 3 level (A=.327, B=.146)	1247	2247	Kings, Amphenol 3-piece
CST black 3 level (A=.344, B=.094)	1248	2248	ADC, Amphenol HDTV

Ordering	
CST frame only	1250
CST memory cartridge only	2245
CST frame only – pre-set for Belden 179DT	1245
CST memory cartridge – pre-set for Belden 179DT	1251

COMPLETE
coaxial connector
cross-reference
available on
our website



2240



2241



2248