


B

A

B


A

PANDUIT P/N	WEIGHT
P06B49M	4.9kg




20 AMP, DOUBLE - POLE ELECTRO
MECHANICAL SWITCH / BREAKER (3) PLACES


REAR VIEW



TOP VIEW



FRONT VIEW



SIDE VIEW

NOTES:


1. IDENTIFICATION:
- | | |
|--------------------|------------------------|
| UNIT TYPE: | BASIC |
| ORIENTATION: | HORIZONTAL, 1U |
| OUTLET QTY&TYPE: | (6) C19 |
| BREAKER QTY&TYPE: | (3) 20AMP, DOUBLE-POLE |
| INPUT VOLTAGE: | 200-240VAC, DELTA |
| INPUT CURRENT: | 30A (24A DERATED) |
| INPUT PHASE: | THREE-PHASE DELTA |
| RATED POWER: | 8.6kVA |
| INPUT PLUG: | NEMA L15-30P |
| INPUT CORD LENGTH: | 3m [10'] |
2. ACCESSORIES:
- POCKET GUIDE
- QTY: (4) M6 X 12 PAN HEAD MACHINE SCREWS
- QTY: (4) M6 CAGED NUT
3. RoHS COMPLIANT
4. VISIT PANDUIT'S ON-LINE CATALOG AT WWW.PANDUIT.COM FOR ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
5. MAXIMUM ALLOWABLE INPUT POWER = 8.6 kW
6. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES

2921-3302 [115.0"-130.0"]
INLET POWER CORD

PLUG
30 AMP, 250V x 3~ DELTA
TWIST LOCK
NEMA L15-30P

SIX (6)
RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

01B	08/21/2017	JIANG	MIM	EDM	REVISED TOLERANCES	P06B49M	
01A	06/28/2017	JIANG	MIM	EDM	INITIAL RELEASE	P06B49M	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY				SIGN	
				DATE	
				PRINT	
TITLE					
BASIC SERIES PDU P06B49M CUSTOMER DRAWING					
ITEM REVISION NAME					
DATASHEET FILE NAME:					
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]				MATERIAL/COLOR:	
 THIRD ANGLE PROJECTION				N/A	
				DRAWING NUMBER: P06B49M_DC	
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	
JIANG	05/24/2017	SEAN	NONE		
				SCALE B	