


B


A

B


A




REAR VIEW



TOP VIEW



FRONT VIEW



SIDE VIEW

PANDUIT P/N	WEIGHT
P36B26M	5.8kg

NOTES:

1. IDENTIFICATION:
- UNIT TYPE:

ORIENTATION:

OUTLET QTY&TYPE:

BREAKER QTY&TYPE:

INPUT VOLTAGE:

INPUT CURRENT:

INPUT PHASE:

RATED POWER:

INPUT PLUG:

INPUT CORD LENGTH:
- BASIC

VERTICAL, MID

(30)C13, (6)C19

(3) 20A,DOUBLE-POLE

100-120/200-240VAC, WYE


30A (24A DERATED)

THREE-PHASE WYE

8.6kVA

NEMA L21-30P

3m [10']
2. ACCESSORIES:
- POCKET GUIDE
3. RoHS COMPLIANT
4. VISIT PANDUIT'S ON-LINE CATALOG AT WWW.PANDUIT.COM FOR ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
5. MAXIMUM ALLOWABLE INPUT POWER = 8.6kW
6. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES




PLUG
30 AMP, 120/208V x 3~ WYE
TWIST LOCK
NEMA L21-30P

SIX (6)
RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320 / C19

THIRTY (30)
RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320 / C13

01B	08/21/2017	DI.ZHAI	MIM	EDM	REVISED TOLERANCES	P36B26M
01A	06/28/2017	DI.ZHAI	MIM	EDM	INITIAL RELEASE	P36B26M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN	
		DATE	
		PRINT	
TITLE		BASIC SERIES PDU P36B26M CUSTOMER DRAWING	
ITEM REVISION NAME			
DATASHEET FILE NAME:			
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:	
 THIRD ANGLE PROJECTION		N/A	
Tolerance(mm) 04<50 ±0.5 50<250 ±1.0 250<500 ±1.5 500<1000 ±2.5 1000<2000 ±4.0		DRAWING NUMBER: P36B26M_DC	
DRAWN BY	DATE	CHK	SCALE
DI.ZHAI	05/24/2017	SEAN	NONE
SHT 1 OF 1		SCALE B	