




PANDUIT P/N	WEIGHT
P42B28M	7.9kg




REAR VIEW



TOP VIEW



FRONT VIEW




SIDE VIEW


NOTES:

- IDENTIFICATION:


UNIT TYPE:	BASIC
ORIENTATION:	VERTICAL, 0U FULL
OUTLET QTY&TYPE:	(36) C13, (6) C19
BREAKER QTY&TYPE:	(3) 20AMP, DOUBLE-POLE
INPUT VOLTAGE:	200-240VAC, DELTA
INPUT CURRENT:	50A (28A DERATED)
INPUT PHASE:	THREE-PHASE DELTA
RATED POWER:	10.0kVA
INPUT PLUG:	HUBBELL CS8365C
INPUT CORD LENGTH:	3m [10']
- ACCESSORIES:
POCKET GUIDE
- RoHS COMPLIANT
- VISIT PANDUIT'S ON-LINE CATALOG AT WWW.PANDUIT.COM FOR ADDITIONAL PRODUCT INFORMATION CONTAINED IN THE SPECIFICATION SHEET AS WELL AS A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- MAXIMUM ALLOWABLE INPUT POWER = 10.0 kW
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES



PLUG
50 AMP, 250V x 3~ DELTA
TWIST LOCK
NEMA CS-8365C



SIX (6) RECEPTACLES
16 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19



THIRTY-SIX (36) RECEPTACLES
10 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE: BASIC SERIES PDU P42B28M CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		N/A
THIRD ANGLE PROJECTION		DRAWING NUMBER: P42B28M_DC
DRAWN BY: KUN	DATE: 05/24/2017	SCALE: NONE
CHK: SEAN	SCALE: NONE	SHT 1 OF 1
ECN		SCALE: B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01B	08/21/2017	KUN	MIM	EDM	REVISED TOLERANCES	P42B28M
01A	06/28/2017	KUN	MIM	EDM	INITIAL RELEASE	P42B28M