





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P24D27M-XXYZ	SEE SHEET 2



20 AMP, DOUBLE-POLE ELECTRO MECHANICAL SWITCH / BREAKER (3) PLACES



BOTTOM VIEW

XX: FINISHED GOOD COLOR
BL =BLACK YL =YELLOW
RD =RED BU =BLUE
WH =WHITE GN =GREEN

Y: INPUT FEED TYPE
1 =TOP-END FED
2 =BOTTOM-END FED

Z: INPUT CORD LENGTH
A =1 METER
B =2 METER
C =3 METER

SPECIFICATION:

1. STANDARD:
- | | |
|----------------------|-----------------------------------|
| UNIT TYPE: | MONITORED INPUT |
| ORIENTATION: | VERTICAL, MID |
| OUTLET QTY&TYPE: | (18) C13, (6) C19 |
| INPUT VOLTAGE: | 200-240VAC |
| INPUT CURRENT: | 30A (24A DERATED) |
| BREAKER QTY&TYPE: | (3) 20AMP, DOUBLE-POLE |
| INPUT PHASE: | THREE-PHASE, DELTA |
| RATED POWER: | 8.6kVA |
| INPUT PLUG: | NEMA L15-30P |
| INPUT POWER CORD: | SEE SHEET 2 FOR PART NUMBER TABLE |
| REGULATORY STANDARD: | RoHS COMPLIANT |
2. ADDITIONAL:
- NONE
3. ACCESSORIES:
- (1) QUICK-START GUIDE

NOTES:

1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
4. FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
5. DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24D27M-XX Y Z

PLUG/RECEPTACLE BLOCK



PLUG
NEMA L15-30P, 3P 4W
30A, 250V, 3-PHASE MAX RATED INPUT
24A DERATED



RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT



RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION DE-CODER UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P24D27M
01A	07/27/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24D27M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL, PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN DATE PRINT	
TITLE INTELLIGENT SERIES PDU P24D27M-XXYZ CUSTOMER DRAWING			
ITEM REVISION NAME:		PANDUIT	
DATASHEET FILE NAME:		MATERIAL/COLOR: N/A	
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN] Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		DRAWING NUMBER: P24D27M_DC	
DRAWN BY GEORGE	DATE 07/27/2017	CHK SEAN	SCALE NONE
SHT 1 OF 2		SCALE B	



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24D27M	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-BL1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-BL1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-RD1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-RD1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-RD1C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-WH1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-WH1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-WH1C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-YL1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-YL1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-YL1C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-BU1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-BU1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-BU1C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-GN1A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-GN1B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-GN1C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-BL2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-BL2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-BL2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-RD2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-RD2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-RD2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-WH2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-WH2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-WH2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-YL2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-YL2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-YL2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-BU2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-BU2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-BU2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg
P24D27M-GN2A	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM/-89MM) 3.3' [+3.5"/-1.75"]	5.0kg
P24D27M-GN2B	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM/-89MM) 6.5' [+7"/-3.5"]	5.4kg
P24D27M-GN2C	VERTICAL,(18) C13,(6) C19,MONITORED INPUT, 200-240V/30A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM/-127MM) 10' [+10"/-5"]	5.8kg

02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION DE-CODER UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P24D27M
01A	07/27/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24D27M
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN	
		DATE	
		PRINT	
TITLE INTELLIGENT SERIES PDU P24D27M-XXYZ CUSTOMER DRAWING			
ITEM REVISION NAME:			
DATASHEET FILE NAME:			
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A	
THIRD ANGLE PROJECTION		DRAWING NUMBER: P24D27M_DC	
DRAWN BY GEORGE	DATE 07/27/2017	CHK SEAN	SCALE NONE
SHT 2 OF 2		SCALE B	

