

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P36G18M-XXYZ	SEE SHEET 2

**SPECIFICATION:**

- STANDARD:
  - UNIT TYPE: MONITORED & SWITCHED PER OUTLET
  - ORIENTATION: VERTICAL, 0U FULL
  - OUTLET QTY & TYPE: (30)C13, (6)C19
  - INPUT VOLTAGE: 200-240VAC
  - INPUT CURRENT: 30A (24A DERATED)
  - BREAKER QTY & TYPE: (2) 20AMP, DOUBLE-POLE
  - INPUT PHASE: SINGLE-PHASE
  - RATED POWER: 5.0 kVA
  - INPUT PLUG: NEMA L6-30P
  - INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE
  - REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL: NONE
- ACCESSORIES: (1) QUICK-START GUIDE


**NOTES:**

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION


**IDENTIFICATION**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P36G18M-XX Y Z


XX: FINISHED GOOD COLOR BL =BLACK YL =YELLOW RD =RED BU =BLUE WH =WHITE GN =GREEN	Y: INPUT FEED TYPE 1 =TOP-END FED 2 =BOTTOM-END FED	Z: INPUT CORD LENGTH A =1 METER B =2 METER C =3 METER
--	---	--




LEFT VIEW



REAR VIEW



RIGHT VIEW



FRONT VIEW

BOTTOM VIEW

**PLUG/RECEPTACLE BLOCK**

PLUG  
NEMA L6 - 30P, 2P 3W  
30A, 250V MAX RATED INPUT  
24A DERATED

RECEPTACLES  
IEC 60320/C19  
16A, 250V MAX RATED OUTPUT

RECEPTACLES  
IEC 60320/C13  
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO I NCLUDE CONFIGURABLE OPTION 'DE-CODER'	P36G18M
01A	10/18/2017	WSJ	MIM	EDM	INITIAL RELEASE	P36G18M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY

SIGN \_\_\_\_\_  
DATE \_\_\_\_\_  
PRINT \_\_\_\_\_

TITLE: INTELLIGENT SERIES PDU  
P36G18M-XXYZ  
CUSTOMER DRAWING

ITEM REVISION NAME: \_\_\_\_\_  
DATASHEET FILE NAME: \_\_\_\_\_

UNLESS OTHERWISE SPECIFIED  
DIMENSIONAL TOLERANCE ARE: mm [IN]

Tolerance(mm)  
0<l<50 ±0.5  
50<l<250 ±1.0  
250<l<500 ±1.5  
500<l<1000 ±2.5  
1000<l<2000 ±4.0

MATERIAL/COLOR: N/A

DRAWING NUMBER: P36G18M\_DC

THIRD ANGLE PROJECTION

DRAWN BY: WSJ DATE: 10/18/2017 CHK: SEAN SCALE: NONE

SHT 1 OF 2 SCALE: B

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P36G18M	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-BL1A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-BL1B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-RD1A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-RD1B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-RD1C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-WH1A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-WH1B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-WH1C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-YL1A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-YL1B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-YL1C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-BU1A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-BU1B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-BU1C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-GN1A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-GN1B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-GN1C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-BL2A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-BL2B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-BL2C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-RD2A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-RD2B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-RD2C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-WH2A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-WH2B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-WH2C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-YL2A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-YL2B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-YL2C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-BU2A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-BU2B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-BU2C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg
P36G18M-GN2A	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	9.2kg
P36G18M-GN2B	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	9.6kg
P36G18M-GN2C	VERTICAL,(30) C13,(6) C19,MONITORED&SWITCHED PER OUTLET, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM-127MM) 10'[+10"/-5"]	9.9kg

B

B

A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN \_\_\_\_\_  
DATE \_\_\_\_\_  
PRINT \_\_\_\_\_

TITLE  
INTELLIGENT SERIES PDU  
P36G18M-XXYZ  
CUSTOMER DRAWING

ITEM REVISION NAME \_\_\_\_\_  
DATASHEET FILE NAME: \_\_\_\_\_

UNLESS OTHERWISE SPECIFIED  
DIMENSIONAL TOLERANCE ARE: mm [IN]

Tolerance(mm)  
0<L<50 ±0.5  
50<L<250 ±1.0  
250<L<500 ±1.5  
500<L<1000 ±2.5  
1000<L<2000 ±4.0

MATERIAL/COLOR: N/A

DRAWING NUMBER: P36G18M\_DC

THIRD ANGLE PROJECTION

DRAWN BY: WSJ DATE: 10/18/2017 CHK: SEAN SCALE: NONE

SHT 2 OF 2 SCALE: B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO I NCLUDE CONFIGURABLE OPTION 'DE-CODER'	P36G18M
01A	10/18/2017	WSJ	MIM	EDM	INITIAL RELEASE	P36G18M

2



1