



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
P24E28M-XXYZ	SEE SHEET 2



LEFT VIEW




REAR VIEW



RIGHT VIEW

FOR LENGTH SEE SHEET 2 PART NUMBER TABLE.



FRONT VIEW

SPECIFICATION:


- 1. STANDARD:
 - UNIT TYPE: MONITORED SWITCHED
 - ORIENTATION: VERTICAL, 0U FULL
 - OUTLET QTY & TYPE: (20) C13, (4) C19
 - INPUT VOLTAGE: 200-240VAC
 - INPUT CURRENT: 30A (24A DERATED)
 - BREAKER QTY & TYPE: (2) 20AMP, DOUBLE-POLE SINGLE-PHASE
 - RATED POWER: 5.0kVA
 - INPUT PLUG: NEMA L6-30P
 - INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE
 - REGULATORY STANDARD: RoHS COMPLIANT
- 2. ADDITIONAL: NONE
- 3. ACCESSORIES: (1) QUICK-START GUIDE

NOTES:

- 1. PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES] .
- 2. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES .
- 3. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART .
- 4. FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL .
- 5. DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24E28M-XX Y Z



BOTTOM VIEW

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY

SIGN		DATE		PRINT	
TITLE INTELLIGENT SERIES PDU P24E28M-XXYZ CUSTOMER DRAWING					
ITEM REVISION NAME					
DATASHEET FILE NAME:					
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]				MATERIAL/COLOR:	
Tolerance(mm)				N/A	
THIRD ANGLE PROJECTION				DRAWING NUMBER: P24E28M_DC	
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 2	
WSJ	07/17/2017	SEAN	NONE	SCALE B	

PLUG/RECEPTACLE BLOCK

PLUG
NEMA L6 - 30P, 2P 3W
30A, 250V MAX RATED INPUT
24A DERATED

RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT

RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION 'DE-CODER'	P24E28M
01A	07/17/2017	WSJ	MIM	EDM	INITIAL RELEASE	P24E28M

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24E28M	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-BL1A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-BL1B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-RD1A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-RD1B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-RD1C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-WH1A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-WH1B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-WH1C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-YL1A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-YL1B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-YL1C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-BU1A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-BU1B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-BU1C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-GN1A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-GN1B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-GN1C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-BL2A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-BL2B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-BL2C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-RD2A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-RD2B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-RD2C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-WH2A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-WH2B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-WH2C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-YL2A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-YL2B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-YL2C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-BU2A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-BU2B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-BU2C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'+10''-5"	10.9kg
P24E28M-GN2A	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM-89MM) 3.3'+3.5''-1.75"	10.1kg
P24E28M-GN2B	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM-89MM) 6.5'+7''-3.5"	10.5kg
P24E28M-GN2C	VERTICAL,(20) C13,(4)C19,MONITORED SWITCHED, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM-127MM) 10'+10''-5"	10.9kg

B

B

A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P24E28M-XXYZ CUSTOMER DRAWING		
ITEM REVISION NAME		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
Tolerance(mm) 0<450 ±0.5 50<4250 ±1.0 250<4500 ±1.5 500<41000 ±2.5 1000<42000 ±4.0		DRAWING NUMBER: P24E28M_DC
THIRD ANGLE PROJECTION	DRAWN BY: WSJ	DATE: 07/17/2017
	CHK: SEAN	SCALE: NONE
		SHT 2 OF 2
		SCALE: B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION 'DE-CODER'	P24E28M
01A	07/17/2017	WSJ	MIM	EDM	INITIAL RELEASE	P24E28M

2



1