

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P24E31M-XXYZ	SEE SHEET 2

**SPECIFICATION:**






- STANDARD:
  - UNIT TYPE: MONITORED SWITCHED
  - ORIENTATION: VERTICAL, 0U, FULL
  - OUTLET QTY&TYPE: (12) C13, (12) C19
  - INPUT VOLTAGE: 200-240VAC
  - INPUT CURRENT: 50A (40A DERATED)
  - BREAKER QTY&TYPE: (6) 20AMP, DOUBLE-POLE
  - INPUT PHASE: THREE-PHASE DELTA
  - RATED POWER: 14.4kVA
  - INPUT PLUG: CS8365C
  - INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE
  - REGULATORY STANDARD: RoHS COMPLIANT
- ADDITIONAL: NONE
- ACCESSORIES: (1) QUICK-START GUIDE

**NOTES:**

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [ INCHES ]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED" CONFIGURATION

**IDENTIFICATION**

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24E31M-XX Y Z



XX: FINISHED GOOD COLOR BL=BLACK YL=YELLOW RD=RED BU=BLUE WH=WHITE GN=GREEN	Y: INPUT FEED TYPE 1=TOP-END FED 2=BOTTOM-END FED	Z: INPUT CORD LENGTH A=1 METER B=2 METER C=3 METER
--	---	---

**PLUG/RECEPTACLE BLOCK**



PLUG  
CS8365C, 3P 4W  
50A, 250V, 3-PHASE DELTA MAX RATED INPUT  
40A DERATED



RECEPTACLES  
IEC 60320/C19  
16A, 250V MAX RATED OUTPUT



RECEPTACLES  
IEC 60320/C13  
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION DE-CODER UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P24E31M
01B	12/14/2017	GEORGE	MIM	EDM	UPDATED DESCRIPTION	P24E31M
01A	10/10/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24E31M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P24E31M-XXYZ CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		N/A
THIRD ANGLE PROJECTION		DRAWING NUMBER: P24E31M_DC
DRAWN BY GEORGE	DATE 10/10/2017	SCALE NONE
CHK SEAN	SHT 1 OF 2	
SCALE NONE		SCALE B

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24E31M	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-BL1A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-BL1B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-RD1A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-RD1B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-RD1C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-WH1A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-WH1B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-WH1C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-YL1A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-YL1B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-YL1C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-BU1A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-BU1B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-BU1C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-GN1A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-GN1B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-GN1C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , TOP-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-BL2A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-BL2B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, BLACK	BLACK (RAL 9005)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-BL2C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-RD2A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-RD2B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, RED	RED (RAL 3020)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-RD2C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-WH2A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, WHITE	WHITE (RAL 9003)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-WH2B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, WHITE	WHITE (RAL 9003)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-WH2C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, WHITE	WHITE (RAL 9003)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-YL2A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-YL2B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-YL2C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-BU2A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-BU2B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, BLUE	BLUE (RAL 5005)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-BU2C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg
P24E31M-GN2A	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 1 METER INPUT CORD, GREEN	GREEN (RAL 6001)	1M(+178MM-89MM) 3.3'[+3.5"/-1.75"]	11.1kg
P24E31M-GN2B	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 2 METER INPUT CORD, GREEN	GREEN (RAL 6001)	2M(+178MM-89MM) 6.5'[+7"/-3.5"]	12.4kg
P24E31M-GN2C	VERTICAL,(12) C13,(12) C19,MONITORED SWITCHED, 200-240V/50A/3 PHASE DELTA , BOTTOM-END FED, 3 METER INPUT CORD, GREEN	GREEN (RAL 6001)	3M(+254MM-127MM) 10'[+10"/-5"]	13.7kg

B

B



A

A

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P24E31M-XYZ CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR: N/A
Tolerance(mm) 0<L<50 ±0.5 50<L<250 ±1.0 250<L<500 ±1.5 500<L<1000 ±2.5 1000<L<2000 ±4.0		DRAWING NUMBER: P24E31M_DC
THIRD ANGLE PROJECTION	DRAWN BY GEORGE	DATE 10/10/2017
	CHK SEAN	SCALE NONE
SHT 2 OF 2		SCALE B

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION DE-CODER UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P24E31M
01B	12/14/2017	GEORGE	MIM	EDM	UPDATED DESCRIPTION	P24E31M
01A	10/10/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24E31M

2



1