





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
P06D18M	12.4kg



SPECIFICATION:

1. STANDARD:

UNIT TYPE:	MONITORED INPUT
ORIENTATION:	HORIZONTAL, 1U
OUTLET QTY&TYPE:	(6) C19
INPUT VOLTAGE:	200-240VAC
INPUT CURRENT:	50A (40A DERATED)
BREAKER QTY&TYPE:	(6) 20AMP, DOUBLE-POLE
INPUT PHASE:	THREE-PHASE DELTA
RATED POWER:	14.4kVA
INPUT PLUG:	CS8365
INPUT POWER CORD:	3m [10'], FRONT FEED
REGULATORY STANDARD:	RoHS COMPLIANT

2. ADDITIONAL:

NONE

3. ACCESSORIES:

- POCKET GUIDE
- QTY: (4) M6 X 12 PAN HEAD MACHINE SCREWS
- QTY: (4) M6 CAGED NUT

NOTES:


- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN INCHES
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL

IDENTIFICATION

PART NUMBER	DESCRIPTION
P06D18M	MI PDU, 40AMP, (6) C19, CS8365C-3M, BLACK

B

A



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
02A	03/20/2020	Leo	MIM	EDM	INPUT PLUG CS8365 WAS SHOWN CS8265	P06D18M
01B	12/14/2017	GEORGE	MIM	EDM	UPDATED DESCRIPTION	P06D18M
01A	09/26/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P06D18M

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.		SIGN
		DATE
		PRINT
TITLE INTELLIGENT SERIES PDU P06D18M CUSTOMER DRAWING		
ITEM REVISION NAME:		
DATASHEET FILE NAME:		
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]		MATERIAL/COLOR:
Tolerance(mm) 01-40 ±0.5 50-125 ±1.0 125-250 ±1.5 250-500 ±2.0 500-1000 ±2.5 1000-42000 ±4.0		N/A
THIRD ANGLE PROJECTION		DRAWING NUMBER: P06D18M_DC
DRAWN BY GEORGE	DATE 09/26/2017	SCALE NONE
CHK SEAN	SHT 1 OF 1	
SCALE NONE		SCALE B

2

1