


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	DIM. A	DIM. B
RAFCBI1	1.73 [43.9]	.25 [6.3]
RAFCBI2	2.73 [69.3]	.22 [5.6]
RAFCBI3	3.73 [94.7]	.19 [4.8]

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. DESIGNED FOR USE WITH STANDARD CROSS SECTION CABLE TIES.
3. DIMENSIONS IN [X] ARE MILLIMETERS.

TITLE		RIGHT ANGLE FLAT CABLE BASE (RAFCBI1,2,3)		CUSTOMER DRAWING	
ITEM REVISION NAME		10B015FZ/03		PANDUIT	
DATASET FILE NAME		10B015FZ_DC/03A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:	
.x ± .2 [5.08] .xxx ± .01 [0.254]				BLACK NYLON	
.xx ± .025 [0.635] ANGLES ± 5 °				DRAWING NUMBER:	
THIRD ANGLE PROJECTION				10B015FZ_DC	
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	
DFA	6/13/16	JHAC	1:1	A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	7/11/17	RVU	DJW	JHAC	UPDATED TOLERANCE IN TITLE BLOCK.	GAECN03955
0	6/13/16	DFA	CLW	JHAC	INITIAL RELEASE	GAECN03816