




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- NOTES:
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
 - DIMENSIONS IN () ARE METRIC.
 - WEIGHT: 16 LB/10 PCS (7257 g/10 PCS)
 - KIT INCLUDES:
 - 1- ANGLED METAL STAMPING
 - 12- FURNITURE FACEPLATE (CFFPL4)
 - 48- MINI-COM TX6A 10GIG JACK MODULE W/CAP
 - 1- INSTRUCTION SHEET
 - 1- TERMINATION TOOL (EGJT-1)
 - 1- SCREW KIT (INCLUDES 4 #12-24 SCREWS)
 - 12- LABEL
 - 12- LABEL COVER
 - RoHS COMPLIANT



PART NUMBER		CPPKLA6ATG48WBL		
TITLE		MINI-COM 48 PORT ANGLED TX6A 10GIG MODULAR PATCH PANEL KIT		
		CUSTOMER DRAWING		
ITEM REVISION NAME		M00742KB/03		
DATASET FILE NAME		M00742KB_DC02/03A		
MATERIAL		SEE NOTE 4		
DRAWING NUMBER		00742KB-02		
THIRD ANGLE PROJECTION				
DRAWN BY		DATE	CHK	SCALE
JSP		6-25-13	MBVE	NONE
SHEET 1 OF 1		SIZE A		

A-SIZE CUSTOMER

03A	3-2-22	BJN	MDJR	MMR	A. NOTE 4: SPECIFIED #12-24 SCREWS REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	M09000PQ
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN